-innomount

Mounting Instructions INNOMOUNT



Systems:

Blaser / CZ550 / Merkel B3-B4-KR1 / Sauer 303 / Sauer 404 / Tikka T3 / Weaver - Picatinny / 12 mm - Prisma / Innogun









1. Mounting on the mounting base

For setting the mount, it must be mounted on the mounting base provided to this end. To do so, loosen or unscrew the two clamping screws (Inbus 1,5mm) fastened to the front of the mounting body and the two adjusting screws (Torx T20) escured by them. Once the adjusting screws ((Torx T20) have been unscrewed and the clamping levers opened to 90°, the mount can at any time be easily mounted onto the mounting base. The mount can beset both with unmounted telescopic sight or with the telescopic sight already mounted on the mounting body.

2. Setting the clamping force

Tightening the two adjusting screws (Torx T20) allows you to set the clamping force. The higher you select the torque, the higher the clamping force and thus the directly related closing and opening force of the clamping lever will be. Choose a torque for the adjustment screws that is high enough to just allow the release buttons to be pressed 2.

3. Locking the setting

There it must be ensured that an even available adjustment range is guaranteed, in which one clamping lever with clamping jaws for clamping screws loosened can be pressed into the mounting base. His has to be done with the assembly body disassembled from the mounting base 4. To secure the adjustment, the clamping screws (Inbus 1,5mm) must be tightened again 3.

4. Mounting the axial stop

The axial stop 7 must, seen in the direction of fire only, be inserted into the dedicated recess in the front. The torque of the fasting screw should be approx. 1,3 Nm. Secure the screw with glue 4.

For the Weaver (4mm) / Picatinny (5,2mm) base. Axial stops are available in widths of 4mm and 5mm. 5mm stops are installed as standard.

5. Torque

	1			
	Sliding Block	M4	max. 3 Nm	(Torx T20)
I	Jpper Ring Screw	M4	max. 3 Nm	(Torx T20)
I	_ower Ring Screw	M3,5	max. 1,9 Nm	(Torx T10)
	Screw Axial-Stop	М3	max. 1,3 Nm	(Inbus 2,5)



Neumühle 8 D-97727 Fuchsstadt Telefon+49 (0) 97 32 / 78 64 66-0Fax+49 (0) 97 32 / 78 64 66-6

www.innogun.de E-Mail info@innogun.de